



**SPECIAL
 HAZARDS
 SPECIAL
 SYSTEMS**

- See Bulletin 700

Description	Part Number	Short Code	List Price
MODEL B1 ACCELERATOR			
B1 Accelerator	6301000300	AE	C\$ 2,954.65
B2 Accelerator Trim	6516000002	ACT	C\$ 1,214.96
B1 - Replacement Parts Kits	6888000100	B1RPK	C\$ 1,003.80
SOLENOID VALVE & PULL BOX/STATIONS			
Solenoid Valve - LV2LBX25 - 24 V DC	6871020000	SOL2	C\$ 1,355.20
Solenoid Valve - LV2LBX15 - 115V AC	6871090000	SOL2A	C\$ 2,076.92
Model A - Hydraulic Manual Pull Box	6981000000	HMBOX	C\$ 950.06
Elect. Man. Emergency Station (Single)	6999990416	BNG1	C\$ 747.88
Elect. Man. Emergency Station (Dbl)	6999990417	BNG1F	C\$ 747.88
MODEL PFC4410 PANEL - TYPE D SYSTEMS			
PFC 4410RC Panel	6990004930	PFCPANEL	C\$ 6,408.53
BATTERIES (2 REQUIRED)			
PS 1270 12 Volt, 7 AMP (UL Systems)	6611112100	BATUL	C\$ 425.63
PS 12120 12 Volt, 12 AMP (FM Systems)	6611111000	BATFM	C\$ 631.90

Description	Part Number	Short Code	List Price
DRAIN ASSEMBLIES			
2 - 1/2" Deluge	6501180302	25DDA	C\$ 1,194.24
4 & 6" Deluge	6501180300		C\$ 1,286.33
2 - 1/2" Preaction	6501180102	25PDA	C\$ 1,361.28
6" Preaction	6501180200	6PDA	C\$ 1,470.55
DRY PILOT ACTUATOR			
Dry Pilot Actuator - Model A	71030000	DPA	C\$ 2,070.01
Dry Pilot Actuator - LP/LDX	71030010	DPADDX	C\$ 2,070.01

Electric Alarm Bells and Supervisory Air Supply

- See Bulletin 700

Description	Part Number	Short Code	List Price
ELECTRIC ALARM BELLS-SYSTEM SENSOR			
6" — 24 VDC	6611220400	6KMS	C\$ 118.51
8" — 24 VDC	6611220500	8KMS	C\$ 150.98
10" — 24VDC	6611220600	10KMS	C\$ 171.84
6" — 120 VAC	6611221100	6KBS	C\$ 118.51
8" — 120 VAC	6611221200	8KBS	C\$ 150.98
10" — 120 VAC	6611221300	10KBS	C\$ 171.84
WBB Weatherproof Back Box	6611660200	WBB	C\$ 64.90
ELECTRIC ALARM BELLS -BRECCO			
BRECCO,6",24V,ELECTRIC BELL	6990023215	6KMSB	C\$ 106.14
BRECCO,8",24V,ELECTRIC BELL	6990023216	8KMSB	C\$ 121.42
BRECCO,10",24V,ELECTRIC BELL	6990023217	10KMSB	C\$ 137.84
BRECCO,6",120V,ELECTRIC BELL	6990018984	6KBSB	C\$ 106.14
BRECCO,8",120V,ELECTRIC BELL	6990023218	8KBSB	C\$ 121.42
BRECCO,10",120V,ELECTRIC BELL	6990019017	10KBSB	C\$ 137.84
BRECCO,#ELBBB,WEATHER PROOF BACK BOX	6990018985	WBBB	C\$ 30.17
SUPERVISORY AIR SUPPLY			
B-SI Air Compressor Panel (110 VAC)	6702010003	BACPS	C\$ 7,882.24
C-SI Air Compressor Panel (220 VAC)	6702020003	CACPS	C\$ 9,229.56
A-2 Owner's Air	6304000135	AMDAG	C\$ 1,854.74
A Owner's Air (factory set 10psi)	6304001110	AMDA10	C\$ 1,854.74
A Owner's Air (factory set 23psi)	6304001123	AMDA23	C\$ 1,854.74
B-1 Individual Compressor	6304010100	AMDBG	C\$ 2,106.87
B Air Compressor Control Assembly	6304012100	AMDB	C\$ 2,106.87
Kit, Sys Con, B-SI/C-SI/NS-PaK	6704030001		C\$ 2,781.32
VALVE SEAT WRENCHES			
4" Model B & BX Deluge Valve	6881240000	W4DV	C\$ 409.71
6" Model B & BX Deluge Valve	6881260000	W6DV	C\$ 439.66

NITROGEN MAINTENANCE DEVICES

- NS-PaK and NS-ASAM
- See Bulletin 254

NS-PAK			
NS-PaK Nitrogen Regulator System	6704030021	NSPAK	C\$11,708.17
NS-ASAM			
Nitrogen Maintenance Device w/Pressure Switch	6704030022	NSASAM	C\$ 7,805.45
NITROGEN REGULATING DEVICE			
NITROGEN REGULATING DEVICE W/SWITCH	6304030101		C\$ 2,319.60
NITROGEN REG DEVICE,GAL W/O SW	6304030100		C\$ 1,766.49

LPC SYSTEMS

Description	Part Number	Short Code	List Price
PREACTION SYSTEM COMPONENTS			
CEL Prescient Panel	6999991602		C\$ 8,316.48
CEL 3.2A Batteries	6999991603		C\$ 482.17
Battery Cabinet	6999991604		C\$ 482.17
LPC Single Interlock Trim	6503001605		C\$ 4,017.64
MISCELLANEOUS ITEMS			
Explosion proof solenoid valve	6999990322	SKINNER #XL2LBX25	C\$ 2,109.27

Description	Part Number	Short Code	List Price
TYPE EPC CONSTRUCTION (VINYL JACKET)			
Protectowire (155°F / 68°C) on Msg Wire	6999995589	PHSC155EPCM	C\$ 3.77
Protectowire (190°F / 88°C)	6999995590	PHSC190EPC	C\$ 2.86
Protectowire (190°F / 88°C) on Msg Wire	6999995591	PHSC190EPCM	C\$ 3.77
Protectowire (220°F / 105°C)	6999995592	PHSC220EPC	C\$ 3.38
Protectowire (220°F / 105°C) on Msg Wire	6999995593	PHSC220EPCM	C\$ 3.77
Protectowire (280°F / 138°C)	6999995594	PHSC280EPC	C\$ 3.38
Protectowire (280°F / 138°C) on Msg Wire	6999995595	PHSC280EPCM	C\$ 3.77
Protectowire (356°F / 180°C) on Msg Wire	6999995596	PHSC356EPCM	C\$ 3.77
TYPE EPN CONSTRUCTION (NYLON OVER VINYL JACKET)			
Protectowire (190°F / 88°C)	6999995597	PHSC190EPN	C\$ 4.70
Protectowire (190°F / 88°C) on Msg Wire	6999995598	PHSC190EPNM	C\$ 5.35
TYPE EPR CONSTRUCTION (POLYPROPYLENE ELASTOMER JACKET)			
Protectowire (155°F / 68°C)	6999995599	PHSC155EPR	C\$ 3.64
Protectowire (155°F / 68°C) on Msg Wire	6999995600	PHSC155EPRM	C\$ 4.03
Protectowire (190°F / 88°C)	6999995601	PHSC190EPR	C\$ 3.64
Protectowire (190°F / 88°C) on Msg Wire	6999995602	PHSC190EPRM	C\$ 4.03
Protectowire (280°F / 138°C)	6999995603	PHSC280EPR	C\$ 4.55
Protectowire (280°F / 138°C) on Msg Wire	6999995604	PHSC280EPRM	C\$ 5.18
Protectowire (356°F / 180°C)	6999995605	PHSC356EPR	C\$ 4.70
Protectowire (356°F / 180°C) on Msg Wire	6999995606	PHSC356EPRM	C\$ 5.35
TYPE TRI CONSTRUCTION DUAL TEMPERATURE TRI-WIRE (VINYL JACKET)			
Protectowire Dual Temp (155/200°F - 68/93°C)	6999995607	PHSC6893TRI	C\$ 3.77
Protectowire Dual Temp (155/200°F - 68/93°C) on Msg Wire	6999995608	PHSC6893TRIM	C\$ 4.16
TYPE XLT CONSTRUCTION (VINYL POLYMER JACKET)			
Protectowire Type XLT (135°F / 57 °C)	6999995582	PHSC135XLT	C\$ 3.64
Protectowire Type XLT (135°F / 57 °C) on MSG Wire	6999995609	PHSC135XLTM	C\$ 3.90

Notes:

• **Standard Packaging**

Standard packaging consists of 500 ft. (152m) coils and spools ranging in length from 2300 ft. (710m) to 3280 ft. (1000m) depending upon model ordered. In general, smaller lengths of 500 ft. or less will be on coils, and longer lengths on spools. The exact length of wire per spool used to complete each order is at the sole discretion of the factory. The policy is to send as few spools / coils as possible based upon stock availability.

• **Custom Lengths**

Custom cut single piece coils in lengths up to 1000 ft. (305m) or spools up to 3280 ft. (1000m) can be provided. Limitations may apply depending upon specific model ordered.

• **Messenger Wire Models**

Messenger wire reduces the maximum length of Protectowire that can be accommodated on a standard spool. Types EPC-M, EPR-M and XLT-M are limited to 2500 ft (762m) per spool. Types EPN-M and TRI-M are limited to 2300 ft. (701m) per spool.

**SPECIAL
HAZARDS
SPECIAL
SYSTEMS**



**Protectowire Linear
Heat Detector (LHD)
Installation
Accessories**

Description	Part Number	Short Code	List Price
COMMERCIAL TYPE ZONE/END-OF-LINE JUNCTION BOXES			
Non-metallic Moisture Proof box w/compression terminals	6999995610	ZB4QCMP	C\$ 48.05
Strain Relief Connector (One each req'd per penetration)	6999995585	SR502	C\$ 11.69
HEAVY DUTY TYPE ZONE/END-OF-LINE JUNCTION BOXES			
Fiberglass NEMA-4X Type JIC Enclosure w/compression terminals	6999995584	ZBHD4QC	C\$ 194.81
Strain Relief Connector (One each req'd per penetration)	6999995585	SR502	C\$ 11.69
WIRING ACCESSORIES			
Splicing Connectors (10/pk, SFTS Sealant Recommended)	6999995586	PWSC	C\$ 15.58
3 Pole Splicing Connectors for TRI-Wire (10/pk, SFTS Sealant Recommended)	6999995611	PWSC3	C\$ 15.58
Splicing Sleeves (10/pk)	6999995612	PWS	C\$ 15.58
Tape Sealant for PWSC Splice Connectors (20-30 splices)	6999995613	SFTS18F	C\$ 23.38
Flexible Leads	6999995614	PFL	C\$ 23.38
Splicing Tape - White	6999995615	35WHITE	C\$ 12.99
Splicing Tape - Red	6999995616	35RED	C\$ 12.99
Splicing Tape - Blue	6999995617	35BLUE	C\$ 12.99
Splicing Tape - Black (Low Temp Tape for freezer applications)	6999995618	33+	C\$ 14.29
Wire Dispensing Reel for Coils	6999995619	SU15	C\$ 272.73
FASTENERS - GENERAL PURPOSE APPLICATIONS			
Clips, Corner, Nylon - White	6999995583	WAWN	C\$ 0.57
Clips, Corner, Polypropylene - Clear	6999995620	WAWP	C\$ 0.52
Clips, Line (Use with Type EPR, EPC, EPN & TRI Protectowire)	6999995621	OHS1	C\$ 0.65
304 Stainless Steel Line Clip w/ 1/4" hole (Use w/ all LHD types)	6999995622	OHSSS	C\$ 2.60
Beam Clamp Assembly (Steel)	6999995623	BC2	C\$ 3.25
Iron Zinc Plated Beam Clamp Assembly (w/ Polypropylene clip)	6999995624	BC3P	C\$ 3.90
Iron Zinc Plated Beam Clamp Assembly (w/ Nylon clip)	6999995625	BC3N	C\$ 3.90
Drive Rings	6999995626	PDR	C\$ 0.39
L-Bracket (Rim Seal Type)	6999995627	RMC2	C\$ 4.55
Stainless Steel L-Bracket (Rim Seal Type)	6999995628	RMC3	C\$ 15.58
Insulated Standoff	6999995629	TR5G	C\$ 12.16
Cable Mount (Requires Sikaflex adhesive)	6999995630	EMSACO	C\$ 1.95
Cable Tie (for EMS-A-CO)	6999995631	PLT1SCO	C\$ 1.04
FASTENERS - CABLE TRAY APPLICATIONS			
Mounting Clip (single piece)	6999995633	HPC2	C\$ 2.60
Mounting Clip Assembly	6999995634	CC2N	C\$ 2.60
Mounting Clip Assembly	6999995635	CC2W	C\$ 2.60
Mounting Clip Assembly	6999995636	CC10N	C\$ 3.25
Mounting Clip Assembly	6999995637	CC10W	C\$ 3.25
Mounting Clip Assembly w/ screw & lock nut	6999995638	CC10NS	C\$ 3.90
Mounting Clip Assembly w/ screw & lock nut	6999995639	CC10WS	C\$ 3.90
FASTENERS - SPRINKLER PIPE MOUNTING			
Pipe Mounting Strap - Nylon (3/4" to 2" pipe)	6999995640	PM3A	C\$ 2.19
Pipe Mounting Strap - Nylon (2-1/2" to 3-1/2" pipe)	6999995641	PM3B	C\$ 1.56
Pipe Mounting Strap - Nylon (4" to 6" pipe)	6999995642	PM3C	C\$ 7.79
MESSENGER WIRE APPLICATIONS			
Eyebolt	6999995643	TR4A	C\$ 2.73
Turnbuckle	6999995644	TR24	C\$ 7.27
304 Stainless Steel Eyebolt	6999995645	TR4AS	C\$ 7.79
304 Stainless Steel Turnbuckle	6999995646	TR24S	C\$ 16.88
TEST EQUIPMENT			
Fault Locator System	6999995647	MFL92	C\$1,207.79
Protectowire Alarm Point Locator Meter Adapter	6999995648	APL90	C\$1,025.97