

GATE VALVES

• See Bulletin 443



OSY L399GG



OSY L399FG

| Description | Part Number | Short Code | List Price |
|--|-------------|------------|-------------|
| RELIABLE OSY - L399GG GROOVED x GROOVED GATE VALVES | | | |
| RASCO,#REL-OSY-L399GG,2",300PSI,GXG | 7M99004056 | 2ROSYGG | € 1,547.88 |
| RASCO,#REL-OSY-L399GG,2.5",300PSI,GXG | 7M99004057 | 25ROSYGG | € 1,607.90 |
| RASCO,#REL-OSY-L399GG,3",300PSI,GXG | 7M99004058 | 3ROSYGG | € 1,706.31 |
| RASCO,#REL-OSY-L399GG,4",300PSI,GXG | 7M99004059 | 4ROSYGG | € 1,966.60 |
| RASCO,#REL-OSY-L399GG,6",300PSI,GXG | 7M99004061 | 6ROSYGG | € 2,996.09 |
| RASCO,#REL-OSY-L399GG,8",300PSI,GXG | 7M99004062 | 8ROSYGG | € 4,933.76 |
| RASCO,#REL-OSY-L399GG,10",300PSI,GXG | 7M99004063 | 10ROSYGG | € 7,415.28 |
| RASCO,#REL-OSY-L399GG,12",300PSI,GXG | 7M99004064 | 12ROSYGG | € 11,012.86 |
| RELIABLE OSY - L399F FLANGE x FLANGE GATE VALVES | | | |
| RASCO,#REL-OSY-L399F,2",300PSI,FXF | 7M99004038 | 2ROSY | € 1,547.88 |
| RASCO,#REL-OSY-L399F,2.5",300PSI,FXF | 7M99004039 | 25ROSY | € 1,607.90 |
| RASCO,#REL-OSY-L399F,3",300PSI,FXF | 7M99004040 | 3ROSY | € 1,706.31 |
| RASCO,#REL-OSY-L399F,4",300PSI,FXF | 7M99004041 | 4ROSY | € 1,966.60 |
| RASCO,#REL-OSY-L399F,6",300PSI,FXF | 7M99004043 | 6ROSY | € 2,996.09 |
| RASCO,#REL-OSY-L399F,8",300PSI,FXF | 7M99004044 | 8ROSY | € 4,933.76 |
| RASCO,#REL-OSY-L399F,10",300PSI,FXF | 7M99004045 | 10ROSY | € 7,415.28 |
| RASCO,#REL-OSY-L399F,12",300PSI,FXF | 7M99004046 | 12ROSY | € 11,012.86 |
| RELIABLE OSY - L399FG FLANGE x GROOVED GATE VALVES | | | |
| RASCO,#REL-OSY-L399FG,2",300PSI,FXG | 7M99004047 | 2ROSYFG | € 1,547.88 |
| RASCO,#REL-OSY-L399FG,2.5",300PSI,FXG | 7M99004048 | 25ROSYFG | € 1,607.90 |
| RASCO,#REL-OSY-L399FG,3",300PSI,FXG | 7M99004049 | 3ROSYFG | € 1,706.31 |
| RASCO,#REL-OSY-L399FG,4",300PSI,FXG | 7M99004050 | 4ROSYFG | € 1,966.60 |
| RASCO,#REL-OSY-L399FG,6",300PSI,FXG | 7M99004052 | 6ROSYFG | € 2,996.09 |
| RASCO,#REL-OSY-L399FG,8",300PSI,FXG | 7M99004053 | 8ROSYFG | € 4,933.76 |
| RASCO,#REL-OSY-L399FG,10",300PSI,FXG | 7M99004054 | 10ROSYFG | € 7,415.28 |
| RASCO,#REL-OSY-L399FG,12",300PSI,FXG | 7M99004055 | 12ROSYFG | € 11,012.86 |
| RELIABLE PIUP - 388 INDICATOR POST UNDERGROUND TYPE | | | |
| RASCO,#REL-PIUP-388,VERTICAL IND POST | 7M99003232 | RVPI | € 3,759.66 |
| RELIABLE W388 INDICATOR POST WALL TYPE | | | |
| RASCO,#REL-PIW-388,WALL-TYPE IND POST | 7M99003233 | RWPI | € 2,506.45 |
| RASCO,STEM/COUP UNIT,WALL-TYPE IND POST | 7M99003657 | | € 312.37 |
| RELIABLE REPLACEMENT HANDWHEEL | | | |
| RASCO,REPL.HANDWHEEL,2"-4" OSY | 7M99003825 | | € 123.44 |
| RASCO,REPL.HANDWHEEL,5"-6" OSY | 7M99003826 | | € 147.77 |
| RASCO,REPL.HANDWHEEL,8" OSY | 7M99003827 | | € 185.17 |
| RASCO,REPL.HANDWHEEL,10"-12" OSY | 7M99003828 | | € 383.45 |
| RASCO,REPL.HANDWHEEL,WALL POST IND | 7M99003829 | | € 383.45 |
| RELIABLE FCV - L501F SWING CHECK VALVE | | | |
| RASCO,#REL-FCV-L501F,2",300PSI,FXF,CHK | 7M99004094 | 2CVF | € 1,116.91 |
| RASCO,#REL-FCV-L501F,2.5",300PSI,FXF,CHK | 7M99004095 | 25CVF | € 1,307.24 |
| RASCO,#REL-FCV-L501F,3",300PSI,FXF,CHK | 7M99004096 | 3CVF | € 1,634.64 |
| RASCO,#REL-FCV-L501F,4",300PSI,FXF,CHK | 7M99004097 | 4CVF | € 2,406.21 |
| RASCO,#REL-FCV-L501F,6",300PSI,FXF,CHK | 7M99004099 | 6CVF | € 4,299.52 |
| RASCO,#REL-FCV-L501F,8",300PSI,FXF,CHK | 7M99004100 | 8CVF | € 7,332.34 |
| RASCO,#REL-FCV-L501F,10",300PSI,FXF,CHK | 7M99004101 | 10CVF | € 10,579.08 |
| RASCO,#REL-FCV-L501F,12",300PSI,FXF,CHK | 7M99004102 | 12CVF | € 14,718.50 |

GATE VALVES / RELIABLE PIV

| Description | Part Number | Short Code | List Price |
|--|-------------|------------|-------------|
| RELIABLE PIV - L388F FLANGE x FLANGE GATE VALVES | | | |
| RASCO,#REL-PIV-L388F,2",300PSI,FXF | 7M99004065 | 2RPIV | € 1,908.74 |
| RASCO,#REL-PIV-L388F,2.5",300PSI,FXF | 7M99004066 | 25RPIV | € 1,908.74 |
| RASCO,#REL-PIV-L388F,3",300PSI,FXF | 7M99004067 | 3RPIV | € 1,908.74 |
| RASCO,#REL-PIV-L388F,4",300PSI,FXF | 7M99004068 | 4RPIV | € 1,908.74 |
| RASCO,#REL-PIV-L388F,6",300PSI,FXF | 7M99004070 | 6RPIV | € 2,909.35 |
| RASCO,#REL-PIV-L388F,8",300PSI,FXF | 7M99004071 | 8RPIV | € 4,829.71 |
| RASCO,#REL-PIV-L388F,10",300PSI,FXF | 7M99004072 | 10RPIV | € 7,230.11 |
| RASCO,#REL-PIV-L388F,12",300PSI,FXF | 7M99004073 | 12RPIV | € 9,990.97 |
| RELIABLE PIV - L388FG FLANGE x GROOVED GATE VALVES | | | |
| RASCO,#REL-PIV-L388FG,2",300PSI,FXG | 7M99004074 | 2RPIVFG | € 1,908.74 |
| RASCO,#REL-PIV-L388FG,2.5",300PSI,FXG | 7M99004075 | 25RPIVFG | € 1,908.74 |
| RASCO,#REL-PIV-L388FG,3",300PSI,FXG | 7M99004076 | 3RPIVFG | € 1,908.74 |
| RASCO,#REL-PIV-L388FG,4",300PSI,FXG | 7M99004077 | 4RPIVFG | € 1,908.74 |
| RASCO,#REL-PIV-L388FG,8",300PSI,FXG | 7M99004080 | 8RPIVFG | € 4,829.71 |
| RASCO,#REL-PIV-L388FG,10",300PSI,FXG | 7M99004081 | 10RPIVFG | € 7,230.11 |
| RASCO,#REL-PIV-L388FG,12",300PSI,FXG | 7M99004082 | 12RPIVFG | € 9,990.97 |
| RELIABLE PIV - L388GG GROOVED x GROOVED GATE VALVES | | | |
| **OBS#REL-PIV-L388GG,2",300PSI,GXG | 7M99004085 | 2RPIVGG | € 1,908.74 |
| RASCO,#REL-PIV-L388GG,2.5",300PSI,GXG | 7M99004086 | 25RPIVGG | € 1,908.74 |
| RASCO,#REL-PIV-L388GG,3",300PSI,GXG | 7M99004087 | 3RPIVGG | € 1,908.74 |
| RASCO,#REL-PIV-L388GG,4",300PSI,GXG | 7M99004088 | 4RPIVGG | € 1,908.74 |
| RASCO,#REL-PIV-L388GG,6",300PSI,GXG | 7M99004090 | 6RPIVGG | € 2,909.35 |
| RASCO,#REL-PIV-L388GG,8",300PSI,GXG | 7M99004091 | 8RPIVGG | € 4,829.71 |
| RASCO,#REL-PIV-L388GG,10",300PSI,GXG | 7M99004092 | 10RPIVGG | € 7,230.11 |
| RASCO,#REL-PIV-L388GG,12",300PSI,GXG | 7M99004093 | 12RPIVGG | € 9,990.97 |
| RELIABLE RBVT THREADED BRONZE BUTTERFLY VALVE | | | |
| RASCO,#REL-BBVT1,1",THRD,300PSI | 7M99004562 | B1R | € 537.92 |
| RASCO,#REL-BBVT125,1.25",THRD,300PSI | 7M99004563 | B125R | € 580.25 |
| RASCO,#REL-BBVT15,1.5",THRD,300PSI | 7M99004564 | B15R | € 621.08 |
| RASCO,#REL-BBVT2,2",THRD,300PSI | 7M99004565 | B2R | € 731.72 |
| RASCO,#REL-BBVT25,2.5",THRD,300PSI | 7M99004566 | B25R | € 932.98 |
| RELIABLE RBVG GROOVED BRONZE VALVE | | | |
| RASCO,#REL-BBVG125,1.25",GRV,300PSI | 7M99004567 | BG125R | € 606.62 |
| RASCO,#REL-BBVG15,1.5",GRV,300PSI | 7M99004568 | BG15R | € 643.37 |
| RASCO,#REL-BBVG2,2",GRV,300PSI | 7M99004569 | BG2R | € 726.75 |
| RASCO,#REL-BBVG25,2.5",GRV,300PSI | 7M99004570 | BG25R | € 853.09 |
| RELIABLE REPLACEMENT HANDWHEEL | | | |
| RASCO,REPL.HANDWHEEL,2"-4" OSY | 7M99003825 | | € 123.44 |
| RASCO,REPL.HANDWHEEL,5"-6" OSY | 7M99003826 | | € 147.77 |
| RASCO,REPL.HANDWHEEL,8" OSY | 7M99003827 | | € 185.17 |
| RASCO,REPL.HANDWHEEL,10"-12" OSY | 7M99003828 | | € 383.45 |
| RASCO,REPL.HANDWHEEL,WALL POST IND | 7M99003829 | | € 383.45 |
| RELIABLE FCV - L501F SWING CHECK VALVE | | | |
| RASCO,#REL-FCV-L501F,2",300PSI,FXF,CHK | 7M99004094 | 2CVF | € 1,116.91 |
| RASCO,#REL-FCV-L501F,2.5",300PSI,FXF,CHK | 7M99004095 | 25CVF | € 1,307.24 |
| RASCO,#REL-FCV-L501F,3",300PSI,FXF,CHK | 7M99004096 | 3CVF | € 1,634.64 |
| RASCO,#REL-FCV-L501F,4",300PSI,FXF,CHK | 7M99004097 | 4CVF | € 2,406.21 |
| RASCO,#REL-FCV-L501F,6",300PSI,FXF,CHK | 7M99004099 | 6CVF | € 4,299.52 |
| RASCO,#REL-FCV-L501F,8",300PSI,FXF,CHK | 7M99004100 | 8CVF | € 7,332.34 |
| RASCO,#REL-FCV-L501F,10",300PSI,FXF,CHK | 7M99004101 | 10CVF | € 10,579.08 |
| RASCO,#REL-FCV-L501F,12",300PSI,FXF,CHK | 7M99004102 | 12CVF | € 14,718.50 |



**RBVT THREADED
BUTTERFLY VALVE**

• See Bulletin 830



**RBVG GROOVED
BRONZE VALVE**

RELIABLE BUTTERFLY VALVES



**BUTTERFLY VALVE
 NORMALLY OPEN**

• See Bulletin 831



**BUTTERFLY VALVE
 NORMALLY
 CLOSED**

• See Bulletin 831

| Description | Part Number | Short Code | List Price |
|---|-------------|------------|------------|
| RELIABLE BFG-300 BUTTERFLY VALVES - GROOVED END - IMPORT | | | |
| RASCO,#RELBFG300,2.5",FM/UL,GG BUTTERFLY | 7M99002653 | 25RBG | € 602.22 |
| RASCO,#RELBFG300,3",FM/UL,GG BUTTERFLY | 7M99002654 | 3RBG | € 624.79 |
| RASCO,#RELBFG300,4",FM/UL,GG BUTTERFLY | 7M99002655 | 4RBG | € 700.07 |
| RASCO,#RELBFG300,6",FM/UL,GG BUTTERFLY | 7M99002656 | 6RBG | €1,008.70 |
| RASCO,#RELBFG300,8",FM,GG BUTTERFLY | 7M99002657 | 8RBG | €1,324.86 |
| RELIABLE BFG-300 BUTTERFLY VALVES - NORMALLY CLOSED | | | |
| RASCO,#RELBFG300NC,2.5",FM/UL,GG BFY NC | 7M99004615 | 25RBGNC | € 620.17 |
| RASCO,#RELBFG300NC,3",FM/UL,GG BFY NC | 7M99004616 | 3RBGNC | € 637.11 |
| RASCO,#RELBFG300NC,4",FM/UL,GG BFY NC | 7M99004617 | 4RBGNC | € 710.85 |
| RASCO,#RELBFG300NC,6",FM/UL,GG BFY NC | 7M99004618 | 6RBGNC | €1,012.37 |
| RASCO,#RELBFG300NC,8",FM/UL,GG BFY NC | 7M99004619 | 8RBGNC | €1,338.69 |
| RELIABLE PIW-388 INDICATOR POST - WALL TYPE | | | |
| PIW-388 WALL TYPE | 7M99003233 | RWPI | €2,506.45 |
| RELIABLE PIUP-388 INDICATOR POST-VERTICAL | | | |
| PIUP-388 VERTICAL | 7M99003232 | RVPI | €3,759.66 |

Notes:

Specify the following when ordering:

- Supervision
- Valve Supervised Open
- Valve Supervised Closed

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.