

## MERIT TEE-LETS



| Description            | Part Number | Short Code | Box Qty | List Price |
|------------------------|-------------|------------|---------|------------|
| <b>M300 - TEE-LETS</b> |             |            |         |            |
| .5 x 1.25-2            | 7M99003845  | 51252O     | 350     | S\$ 19.42  |
| .5 x 2-2.5"            | 7703020810  | 5225O      | 350     | S\$ 19.42  |
| .5 x 2.5-8"            | 7703021032  | 5258O      | 350     | S\$ 19.42  |
| .75 x 1.25-2"          | 7M99003455  | 751252O    | 250     | S\$ 19.42  |
| .75 x 2-2.5"           | 7707030810  | 75225O     | 250     | S\$ 19.42  |
| .75 x 2.5-8"           | 7707031032  | 75258O     | 250     | S\$ 19.42  |
| 1 x 1.25-1.5"          | 7709040506  | 112515O    | 175     | S\$ 28.20  |
| 1 x 1.5-2"             | 7709040608  | 1152O      | 175     | S\$ 28.20  |
| 1 X 2-2.5"             | 7709040810  | 1225O      | 175     | S\$ 28.20  |
| 1 x 2.5-4"             | 7M99003457  | 1254O      | 175     | S\$ 28.20  |
| 1 x 5-8"               | 7709042032  | 158O       | 175     | S\$ 28.20  |
| 1.25 x 1.5-2"          | 7711050608  | 125152O    | 95      | S\$ 47.36  |
| 1.25 x 2-2.5"          | 7711050810  | 125225O    | 95      | S\$ 47.36  |
| 1.25 x 2.5-3"          | 7711051012  | 125253O    | 95      | S\$ 47.36  |
| 1.25 x 3-4"            | 7711051216  | 12534O     | 95      | S\$ 47.36  |
| 1.25 x 5-8"            | 7711052032  | 12558O     | 95      | S\$ 47.36  |
| 1.5 x 1.5"             | 7713060600  | 1515O      | 65      | S\$ 57.04  |
| 1.5 x 2"               | 7713060800  | 152O       | 65      | S\$ 57.04  |
| 1.5 x 2.5"             | 7713061000  | 1525O      | 65      | S\$ 57.04  |
| 1.5 x 3-4"             | 7713061216  | 1534O      | 65      | S\$ 57.04  |
| 1.5 x 4"               | 7713061600  | 154O       | 65      | S\$ 57.04  |
| 1.5 x 5-8"             | 7713062032  | 1558O      | 65      | S\$ 57.04  |
| 2 x 2"                 | 7715080800  | 22O        | 35      | S\$ 75.24  |
| 2 x 2.5"               | 7715081000  | 225O       | 35      | S\$ 75.24  |
| 2 x 3"                 | 7715081200  | 23O        | 35      | S\$ 75.24  |
| 2 x 4"                 | 7715081600  | 24O        | 35      | S\$ 75.24  |
| 2 x 5"                 | 7715082000  | 25O        | 35      | S\$ 75.24  |
| 2 x 6"                 | 7715082400  | 26O        | 35      | S\$ 75.24  |
| 2 x 8"                 | 7715083200  | 28O        | 35      | S\$ 75.24  |

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

## MERIT TEE-LETS



| Description             | Part Number | Short Code | Box Qty | List Price |
|-------------------------|-------------|------------|---------|------------|
| <b>TEE-LETS (CONT.)</b> |             |            |         |            |
| 2.5 x 2.5"              | 7717101000  | 2525O      | 20      | S\$ 136.94 |
| 2.5 x 3"                | 7717101200  | 253O       | 20      | S\$ 136.94 |
| 2.5 x 4"                | 7717101600  | 254O       | 20      | S\$ 136.94 |
| 2.5 x 5"                | 7717102000  | 255O       | 20      | S\$ 136.94 |
| 2.5 x 6"                | 7717102400  | 256O       | 20      | S\$ 136.94 |
| 2.5 x 8"                | 7717103200  | 258O       | 20      | S\$ 136.94 |
| 3 x 3"                  | 7719121200  | 33O        | 10      | S\$ 263.37 |
| 3 x 4"                  | 7719121600  | 34O        | 10      | S\$ 263.37 |
| 3 x 6"                  | 7719122400  | 36O        | 10      | S\$ 263.37 |
| 3 x 8"                  | 7719123200  | 38O        | 10      | S\$ 263.37 |
| 4 x 4"                  | 7721161600  | 44O        | 10      | S\$ 422.70 |
| 4 x 6"                  | 7721162400  | 46O        | 10      | S\$ 422.70 |
| 4 x 8"                  | 7721163200  | 48O        | 10      | S\$ 422.70 |

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

## MERIT TEE-LETS



| Description                                       | Part Number | Short Code | Box Qty | List Price |
|---|-------------|------------|---------|------------|
| <b>MERIT GROOVED SHAPED NIPPLES - SCHEDULE 40</b> |             |            |         |            |
| 1.25 x 1.25"                                      | 7607050500  | 125125GSN  | 80      | S\$ 60.68  |
| 1.25 x 1.5"                                       | 7607050600  | 12515GSN   | 80      | S\$ 60.68  |
| 1.25 x 2-2.5"                                     | 7607050810  | 125225GSN  | 80      | S\$ 60.68  |
| 1.25 x 3-4"                                       | 7607051216  | 12534GSN   | 80      | S\$ 60.68  |
| 1.25 x 5-8"                                       | 7607052032  | 12558GSN   | 80      | S\$ 60.68  |
| 1.5 x 1.5"  | 7609060600  | 1515GSN    | 50      | S\$ 65.56  |
| 1.5 x 2"  | 7609060800  | 152GSN     | 50      | S\$ 65.56  |
| 1.5 x 2.5"  | 7609061000  | 1525GSN    | 50      | S\$ 65.56  |
| 1.5 x 3-4"  | 7609061216  | 1534GSN    | 50      | S\$ 65.56  |
| 1.5 x 5-8"  | 7609062032  | 1558GSN    | 50      | S\$ 65.56  |
| 2 x 2"  | 7611080800  | 22GSN      | 30      | S\$ 71.09  |
| 2 x 2.5"  | 7611081000  | 225GSN     | 30      | S\$ 71.09  |
| 2 x 3"  | 7611081200  | 23GSN      | 30      | S\$ 71.09  |
| 2 x 4"  | 7611081416  | 24GSN      | 30      | S\$ 71.09  |
| 2 x 5"  | 7611082000  | 25GSN      | 30      | S\$ 71.09  |
| 2 x 6"  | 7611082400  | 26GSN      | 30      | S\$ 71.09  |
| 2 x 8"  | 7611083200  | 28GSN      | 30      | S\$ 71.09  |
| 2.5 x 2.5"  | 7627101000  | 2525SN4    | 20      | S\$ 100.59 |
| 2.5 x 3"  | 7627101200  | 253SN4     | 20      | S\$ 100.59 |
| 2.5 x 3.5-4"                                      | 7627101416  | 25354SN4   | 20      | S\$ 100.59 |
| 2.5 x 5"  | 7627102000  | 255SN4     | 20      | S\$ 100.59 |
| 2.5 x 6"  | 7627102400  | 256SN4     | 20      | S\$ 100.59 |
| 2.5 x 8"  | 7627103200  | 258SN4     | 20      | S\$ 100.59 |
| 3 x 3"  | 7629121200  | 33SN4      | 15      | S\$ 131.64 |
| 3 x 3.5"  |             |            | 15      | S\$ Call   |
| 3 x 4"  | 7629121600  | 34SN4      | 15      | S\$ 131.64 |
| 3 x 5"  | 7629122000  | 35SN4      | 15      | S\$ 131.64 |
| 3 x 6"  | 7629122400  | 36SN4      | 15      | S\$ 131.64 |
| 3 x 8"  | 7629123200  | 38SN4      | 15      | S\$ 131.64 |
| 4 x 4"  | 7631161600  | 44SN4      | 5       | S\$ 205.46 |
| 4 x 5"  | 7631162000  | 45SN4      | 5       | S\$ 205.46 |
| 4 x 6"  | 7631162400  | 46SN4      | 5       | S\$ 205.46 |
| 4 x 8"  | 7631163200  | 48SN4      | 5       | S\$ 205.46 |
| 6 x 6"  | 7635242400  | 66SN4      | 2       | S\$ 416.53 |
| 6 x 8"  | 7635243200  | 68SN4      | 2       | S\$ 416.53 |
| 8 x 8"  | 7637323200  | 88SN4      | 1       | S\$ 526.79 |

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

## MERIT TEE-LETS



| Description                                       | Part Number | Short Code | Box Qty | List Price |
|---|-------------|------------|---------|------------|
| <b>MERIT GROOVED SHAPED NIPPLES - SCHEDULE 10</b> |             |            |         |            |
| 2.5 x 2.5"  | 7613101000  | 2525GSN    | 20      | S\$ 86.42  |
| 2.5 x 3"  | 7613101200  | 253GSN     | 20      | S\$ 86.42  |
| 2.5 x 4"  | 7613101416  | 254GSN     | 20      | S\$ 86.42  |
| 2.5 x 5"  | 7613102000  | 255GSN     | 20      | S\$ 86.42  |
| 2.5 x 6"  | 7613102400  | 256GSN     | 20      | S\$ 86.42  |
| 2.5 x 8"  | 7613103200  | 258GSN     | 20      | S\$ 86.42  |
| 3 x 3"  | 7615121200  | 33GSN      | 15      | S\$ 117.43 |
| 3 x 3.5"  | 7615121416  | 335GSN     | 15      | S\$ 117.43 |
| 3 x 4"  | 7615121600  | 34GSN      | 15      | S\$ 117.43 |
| 3 x 5"  | 7615122000  | 35GSN      | 15      | S\$ 117.43 |
| 3 x 6"  | 7615122400  | 36GSN      | 15      | S\$ 117.43 |
| 3 x 8"  | 7615123200  | 38GSN      | 15      | S\$ 117.43 |
| 4 x 4"  | 7619161600  | 44GSN      | 5       | S\$ 166.51 |
| 4 x 5"  | 7619162000  | 45GSN      | 5       | S\$ 166.51 |
| 4 x 6"  | 7619162400  | 46GSN      | 5       | S\$ 166.51 |
| 4 x 8"  | 7619163200  | 48GSN      | 5       | S\$ 166.51 |
| 6 x 6"  | 7623242400  | 66GSN      | 2       | S\$ 366.22 |
| 6 x 8"  | 7623243200  | 68GSN      | 2       | S\$ 366.22 |

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

## IMPORT OLETS



| Description                      | Part Number | Short Code | Box Qty | List Price |
|----------------------------------|-------------|------------|---------|------------|
| <b>MTM-40 ANVIL IMPORT OLETS</b> |             |            |         |            |
| STAR,MTM-40,.5 X 1.25-2,O-LET    | 7M99003847  | 51252OS    | 400     | S\$ 15.72  |
| STAR,MTM-40,.5 X 2-2.5,O-LET     | 7S03020810  | 5225OS     | 400     | S\$ 15.72  |
| STAR,MTM-40,.5 X 2.5-8,O-LET     | 7S03021032  | 5258OS     | 240     | S\$ 15.72  |
| STAR,MTM-40,.75 X 1.25"-2",OLET  | 7M99003543  | 751252OS   | 240     | S\$ 15.72  |
| STAR,MTM-40,3/4X2-2.5,O-LET      | 7S07030810  | 75225OS    | 160     | S\$ 15.72  |
| STAR,MTM-40,.75 X 2.5-8,O-LET    | 7S07031032  | 75258OS    | 160     | S\$ 15.72  |
| STAR,MTM-40,1 X 1.25 - 1.5,O-LET | 7S09040506  | 112515OS   | 160     | S\$ 22.94  |
| STAR,MTM-40,1 X 1.5 - 2,O-LET    | 7S09040608  | 1152OS     | 160     | S\$ 22.94  |
| STAR,MTM-40,1X2-2.5,O-LET        | 7S09040810  | 1225OS     | 90      | S\$ 22.94  |
| STAR,MTM-40,1" X 2.5"-4",OLET    | 7M99003545  | 1254OS     | 90      | S\$ 22.94  |
| STAR,MTM-40,1 X 5-8,O-LET        | 7S09042032  | 158OS      | 90      | S\$ 22.94  |
| STAR,MTM-40,1.25 X 1.25,O-LET    | 7S11050500  | 125125OS   | 90      | S\$ 38.87  |
| STAR,MTM-40,1.25X1.5-2,O-LET     | 7S11050608  | 125152OS   | 70      | S\$ 38.87  |
| STAR,MTM-40,1.25 X 2-2.5,O-LET   | 7S11050810  | 125225OS   | 70      | S\$ 38.87  |
| STAR,MTM-40,1.25X2.5-3,O-LET     | 7S11051012  | 125253OS   | 70      | S\$ 38.87  |
| STAR,MTM-40,1.25X3-4,O-LET       | 7S11051016  | 12534OS    | 70      | S\$ 38.87  |
| STAR,MTM-40,1.25 X 5-8,O-LET     | 7S11052032  | 12558OS    | 70      | S\$ 38.87  |
| STAR,MTM-40,1.5 X 1.5,O-LET      | 7S13060600  | 1515OS     | 70      | S\$ 47.03  |
| STAR,MTM-40,1.5 X 2,O-LET        | 7S13060800  | 152OS      | 40      | S\$ 47.03  |
| STAR,MTM-40,1.5 X 2.5,O-LET      | 7S13061000  | 1525OS     | 40      | S\$ 47.03  |
| STAR,MTM-40,1.5X3-4,O-LET        | 7S13061216  | 1534OS     | 40      | S\$ 47.03  |
| STAR,MTM-40,1.5 X 4,O-LET        | 7S13061600  | 154OS      | 40      | S\$ 47.03  |
| STAR,MTM-40,1.5X5-8,O-LET        | 7S13062032  | 1558OS     | 40      | S\$ 47.03  |
| STAR,MTM-40,2 X 2,O-LET          | 7S15080800  | 22OS       | 40      | S\$ 62.14  |
| STAR,MTM-40,2 X 2.5,O-LET        | 7S15081000  | 225OS      | 40      | S\$ 62.14  |
| STAR,MTM-40,2X3,O-LET            | 7S15081200  | 23OS       | 40      | S\$ 62.14  |
| STAR,MTM-40,2X4,O-LET            | 7S15081600  | 24OS       | 40      | S\$ 62.14  |
| STAR,MTM-40,2 X 6,O-LET          | 7S15082400  | 26OS       | 40      | S\$ 62.14  |
| STAR,MTM-40,2 X 8,O-LET          | 7S15083200  | 28OS       | 40      | S\$ 62.14  |

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.

# Σ SIGMA

## Piping Products

| Description                | Part Number | Short Code | List Price |
|----------------------------|-------------|------------|------------|
| <b>SLIP ON WELD FLANGE</b> |             |            |            |
| 2" (6OD)                   | 6999992899  | 2SWF       | S\$ 96.13  |
| 2-1/2" (7OD)               | 6999992900  | 25SWF      | S\$ 134.58 |
| 3" (7-1/2OD)               | 6999992901  | 3SWF       | S\$ 147.15 |
| 4" (9OD)                   | 6999992902  | 4SWF       | S\$ 200.63 |
| 6" (11OD)                  | 6999992903  | 6SWF       | S\$ 310.14 |
| 8" (13-1/2OD)              | 6999992904  | 8SWF       | S\$ 425.28 |
| 10" (16OD)                 | 6999992905  | 10SWF      | S\$ 507.75 |
| 12" (19OD)                 | 6999992906  | 12SWF      | S\$ 884.13 |

Items shown on this sheet may not be stocked at all Reliable warehouses. Please contact your local Reliable Warehouse for Availability. Refer to technical data sheets for specific listings, approvals and design parameters.