

Description	Part Number	List Price
MODEL A — 2 1/2" DELUGE VALVE		
Socket Flat Head Screw - Need to order 6	95616402	\$ 27.67
Socket Head Cap Screw - Need to order 8	95606402	\$ 27.67
Rubber Facing	92206402	\$ 356.25
Clamping Ring	95306402	\$ 449.81
Rubber Seal	93406402	\$ 106.42
Cover Bolts - Need to order 8	91106123	\$ 5.22
MODEL B — 4" DELUGE VALVE		
Cover Gasket	93706404	\$ 124.98
Cover Bolts -Need to order 6	91106404	\$ 6.31
Seat "O" Ring	95406404	\$ 15.77
Clapper Clamping Ring	95306404	\$ 224.96
Clapper Rubber Facing	93406404	\$ 474.43
Clamping Ring Screws -Need to order 4	95606404	\$ 31.92
Drain Plug	98604403	\$ 31.92
"E" Ring, Pin Lever - Need to order 2	95316408	\$ 69.05
Lever Shaft	96216404	\$ 219.02
Lever Shaft Model BX	96216424	\$ 156.41
"O" Ring, Push Rod	95406406	\$ 25.48
"O" Ring, Push Rod	95406407	\$ 25.61
"O" Ring, Push Rod Guide	95406408	\$ 44.17
Push Rod Spring	96406406	\$ 219.02
Push Rod Cover Gasket	93716406	\$ 31.92

Important Note:

Above parts are 1241 and subsequent, 1240 and prior requires replacements part kit

Description	Part Number	List Price
MODEL B — 4" DELUGE VALVE		
Push Rod Cover Assembly ¹	71040419	\$ 811.51
MODEL B — 6" DELUGE VALVE		
Cover Gasket	93706406	\$ 137.24
Cover	92106406	\$ 811.51
Cover Bolts - Need to order 8	91106406	\$ 6.31
Push Rod Cover	92126408	\$ 262.71
Seat "O" Ring	95436126	\$ 15.90
Clapper Clamping Ring	95306406	\$ 237.71
Clapper Shaft	96206406	\$ 237.71
Clapper Rubber Facing	93406406	\$ 487.05
Clamper Ring Screws - Need to order 4	95606406	\$ 37.74
"E" Ring, Pin Lever - Need to order 2	95316407	\$ 124.98
Lever Shaft	96216406	\$ 237.71
"O" Ring, Push Rod	95406406	\$ 25.48
"O" Ring, Push Rod	95406407	\$ 25.61
"O" Ring, Push Rod Guide	95406408	\$ 44.17
Push Rod Cover Gasket	93716406	\$ 31.92
Drain Plug	98604403	\$ 31.92
Push Rod Spring	96406406	\$ 219.02
Push Rod Cover Assembly ¹	71040419	\$ 811.51

¹ Contains:

Push Rod Cover, Inlet Orifice

Important Note:

Above parts are 1239 and subsequent, 1239 and prior requires replacements part kit

Description	Part Number	List Price
MODEL DDX — 2", 2-1/2" & 3" DELUGE VALVES		
Cover, Pushrod, Assembly	71040416	\$ 751.45
Clapper Assembly	71041300	\$ 2,497.26
Screw, Hex Cap. 1/2-13 x 1-1/4", ZN PLTD, Grade A	91106123	\$ 5.22
Mounting Ring, Machined	91306013	\$ 191.11
Seal Assembly	93416003	\$ 106.42
Gasket, Access Cover	93706003	\$ 115.88
Pushrod, Guide	93916006	\$ 107.39
Knob, Reset, Assembly	94356007	\$ 121.82
Piston, Machined	95106006	\$ 737.13
Diaphragm	95276006	\$ 75.60
Clip, Retaining, 3/8" Shaft	95306268	\$ 12.13
O-Ring - Need to order 114	95406007	\$ 25.61
O-Ring - Need to order 912	95406024	\$ 25.61
O-Ring - Need to order 014	95406407	\$ 25.61
O-Ring - Need to order 150	95406410	\$ 25.61
O-Ring - Need to order 147	95406411	\$ 25.61
Screw, Socket Head, 1/4"-20 x 5/8"	95606114	\$ 27.79
Screw, Cap. #6-32 x 1/2", SS	95606133	\$ 27.79
Seat Machined	96016003	\$ 717.00
Pin. Hinge	96206003	\$ 101.32
Pin. Lever	96216003	\$ 406.36
Spacer, Clapper Pin	96310003	\$ 101.32
Spring, Lever	96406003	\$ 54.73
Spring, DDX	96406906	\$ 60.80
Washer, Lock, # 6, SS	96906112	\$ 2.91

Important Note:

Above parts are 1239 and subsequent, 1239 and prior requires replacements part kit

Description	Part Number	List Price
DDV REPLACEMENT PARTS		
ASSY,DIAPHRAGM,DDV,2 1/2&3	95277630	\$ 428.00
ASSY,DIAPHRAGM,DDV,4	95277640	\$ 856.00
ASSY,DIAPHRAGM,DDV,6	95277660	\$ 1,819.00
SCR,HEX,1/2-13X1,ZINC	95606179	\$ 7.50
SCR,HEX,5/8-11X1,ZINC	95606182	\$ 7.50
SCR,HEX,7/8-9X1-1 1/2,ZINC	95606180	\$ 10.00
STUD,7/8-9X3,ZINC	96506604	\$ 8.56
NUT,HEX,7/8"-9	94906924	\$ 6.00

Description	Part Number	List Price
MODEL DDX — 4", & 6", DELUGE VALVES		
Cover, Pushrod, Assembly	71040416	\$ 751.45
Seat, 4"	96016004	\$ 710.32
Clapper, 4"	91916004	\$ 2,497.26
Cover, 4"	92116064	\$ 635.82
Seal Faceplate Subassembly, 4"		\$ Call
Gasket, Cover, 4"	93706004	\$ 115.88
Lever, 4"	94506004	\$ 125.83
Seat, 6"	96016006	\$ 749.27
Clapper, 6"	91916006	\$ 3,558.11
Cover, 6"	92116066	\$ 710.93
Seal Faceplate Subassembly, 6"		\$ Call
Gasket, Cover, 6"	93706006	\$ 150.10
Lever, 6"		\$ Call
O-ring - Need to order 014	95406407	\$ 25.61
O-ring - Need to order 114	95406007	\$ 25.61
O-ring - Need to order 161		\$ Call
O-ring - Need to order 912	95406024	\$ 25.61
Gasket, Clapper, 4"		\$ Call
Gasket, Clapper, 6"		\$ Call
Hinge Pin, Clapper	96216086	\$ 101.32
Pin, Lever		\$ Call
Threaded Stud, #10-32 x 3/4"		\$ Call
Pin, Locking, Seat		\$ Call
Piston	95106006	\$ 737.13
Plug, Socket, Ø 3/8"-18 NPT		\$ Call
Pushrod	95506006	\$ 497.49
Pushrod Guide	93916006	\$ 107.39
Ring, Retaining (2 Assembled to Item No.14)	95306267	\$ 11.16
Screw, Button Head, #10-32 x 3/8 - 4" use		\$ Call
Screw, Hex Washer Head, #10-32 x 3/8" - 6" use		\$ Call
Screw, Hex Cap, Ø 1/2"-13 x 1-1/2"	95606107	\$ 27.79
Screw, Hex Cap, Ø 5/8"-11 x 1-3/4"	91106006	\$ 27.79
Spring Lock Washer, #10	96906111	\$ 2.91
Screw, C'sunk Cap Head, Ø 3/8"-16 x 3/4"	95606127	\$ 27.79
Screw, Socket Head, #10-32 x 1"	95606130	\$ 27.79
Screw, Socket Head, Ø 1/4"-20 x 5/8"	95606114	\$ 27.79
Spring, Lever	96406004	\$ 54.73
Spring	96406906	\$ 60.80
Diaphragm	95276006	\$ 75.60
Knob, Reset, Assembly	94356007	\$ 121.82

Description	Part Number	List Price
MODEL DDX — 8" DELUGE VALVE		
Pushrod Cover Assembly	71040416	\$ 751.45
O-Ring - Need to order 256	95406414	\$ 25.61
Screw, Hex Cap, 5/8-11x2"	95606110	\$ 33.37
Mounting Ring, Machined	91306018	\$ 48.66
Clapper, Machined	91916008	\$ 3,722.05
Access Cover	92116068	\$ 139.06
Seal Assembly	93416008	\$ 245.83
Gasket, Access Cover	93706008	\$ 150.10
Bumpstop Assembly	93722000	\$ 106.29
Pushrod Guide	93916006	\$ 107.39
Lever	94506008	\$ 899.00
Striker	95006410	\$ 884.44
Piston	95106006	\$ 737.13
Diaphragm	95276006	\$ 75.60
Retaining Clip, 3/4" Shaft	95316408	\$ 69.05
O-Ring - Need to order 114	95406007	\$ 25.61
O-Ring - Need to order 912	95406024	\$ 25.61
O-Ring - Need to order 260	95406407	\$ 25.61
O-Ring - Need to order 259	95406413	\$ 25.61
Screw, Socket Head, 1/4-20 x 5/8"	95606114	\$ 27.79
Screw, Socket Head, #10-32 x 1"	95606130	\$ 27.79
Seat, Machined	96016008	\$ 860.41
Hinge Pin	96206008	\$ 121.58
Lever Pin	96216008	\$ 497.97
Clapper Spacer	96310008	\$ 121.58
Lever Spring	96406008	\$ 65.64
DDX Spring	96406906	\$ 60.80
Spring Lock Washer, #10	96906111	\$ 2.91
Screw, Socket Cap, Flat Head, 1/2-13 x 3/4"	95606135	\$ 25.00
Reset Knob Assembly	94356007	\$ 121.82

Description	Part Number	List Price
MODEL DDX — 8" STAINLESS STEEL DELUGE VALVE		
Pushrod Cover	92126358	\$ 334.54
O-Ring - Need to order 266	95406414	\$ 25.61
Screw, Hex Cap, 5/8-11x2"	95606137	\$ 33.37
Mounting Ring, Machined	91326018	\$ 48.66
Clapper, Machined	91926008	\$ 4,022.60
Access Cover	92126069	\$ 150.35
Seal Assembly	93416028	\$ 263.06
Gasket, Access Cover	93706008	\$ 150.10
Bumpstop Assembly	93722000	\$ 106.29
DDX:PUSHROD GUIDE	93916006	\$ 107.39
LEVER,8" DDX VALVE 6-4, GRADE 5	94506028	\$ 1,049.09
Striker	95006411	\$ 901.79
Piston	95106006	\$ 737.13
Diaphragm	95276006	\$ 75.60
Retaining Clip, 3/4" Shaft	95316408	\$ 69.05
O-Ring - Need to order 114	95406007	\$ 25.61
O-Ring - Need to order 912	95406024	\$ 25.61
O-Ring - Need to order 260	95406407	\$ 25.61
O-Ring - Need to order 259	95406413	\$ 25.61
Screw, Socket Head, 1/4-20 x 5/8"	95606114	\$ 27.79
Screw, Socket Head, #10-32 x 1"	95606130	\$ 27.79
Seat, Machined	96026008	\$ 889.78
Hinge Pin	96206008	\$ 121.58
Lever Pin	96216008	\$ 497.97
Clapper Spacer	96310008	\$ 121.58
Lever Spring	96406008	\$ 65.64
DDX Spring	96406906	\$ 60.80
Spring Lock Washer, #10	96906111	\$ 2.91
Screw, Socket Cap, Flat Head, 1/2-13 x 3/4"	95606135	\$ 25.00
Reset Knob Assembly	94356009	\$ 151.80

Description	Part Number	List Price
MODEL BX — 4" & 6" EXTERNAL RESET DEVICE		
Reset Knob Ext. Reset Del Mod. B 4" & 6"	94356426	\$ 131.29
"O" Ring Shaft Ext. Reset 4" & 6" Del	95406425	\$ 3.88
"O" Ring Bearing 4" & 6" Del Mod. B Ext. Res.		\$ Call
Screw Spring 4" Del Ext. Reset	95606424	\$ 6.79
Lever Screw Ext Reset Del Valve 4" & 6"	95606426	\$ 44.17
Stud Threaded, BX 4" & 6" Del Ext. Reset		\$ Call
Clapper Spring, 4" & 6" Del BX	96406426	\$ 44.17
MODEL B — DELUGE VALVE TRIM PARTS		
Drip Cup, Support Clip Bolt, Nut & Screw	71010471	\$ 274.95
Strainer 3/4"	78650200	\$ 261.36
Stop Cock Valve 1/2"	78650300	\$ 237.71
Ball Drip Valve 1/2" Mechanical Mod. C	78653100	\$ 444.71
Strainer 1/4"	98727605	\$ 193.66
Angle Valve 2"	98840100	\$ 443.49
Horizontal Check Valve 1/4"	98840143	\$ 256.27
Globe Valve 1/2"	98840171	\$ 224.96
Horizontal Check Valve 1/2"	98840181	\$ 246.08
Globe Valve 1/4"	98840172	\$ 219.02
Pressure Switch	98728800	\$ 1,030.05
Restrictor Check Valve	98840141	\$ 331.25
Air Pressure Gauge	98248000	\$ 111.20
Water Pressure Gauge	98248001	\$ 104.00
1/4" 3 Way Bronze Gauge Valve - Need to order 2	98840160	\$ 187.23
Relief Valve Bronze 1/2"	98840190	\$ 256.27
Actuator Diaphragm	92206311	\$ 94.16
Actuator Face Plate	95106901	\$ 106.42
Actuator Face Plate Assembly	95106911	\$ 94.16
1/4" 3 Way Bronze Gauge Valve	98840160	\$ 187.23
MODEL A 2 — AUTOMATIC AIR MAINTENANCE DEVICE		
Regulator	98681630	\$ 587.03
Strainer 1/4"	98727606	\$ 181.28
Check Valve 1/4"	96816902	\$ 262.71
Globe Valve 3/4"	98840170	\$ 256.27
Globe Valve 1/4" - Need to order 2	98840172	\$ 219.02
Restriction Nipple 1/4"	98523100	\$ 56.43