

## ACCESSORIES

### CABINETS

Description	Part Number	Short Code	List Price
<b>A4 EMERGENCY CABINETS FOR LL RESIDENTIAL SPRINKLERS</b>			
3 Capacity	6999991473	3CAB	\$ 100.15
6 Capacity	6999991470	6CAB	\$ 100.15
6 Capacity (Large)	6999991472	6LCAB	\$ 179.41
12 Capacity	6999991471	12CAB	\$ 124.25
<b>A3 EMERGENCY CABINETS FOR RECESSED, CONCEALED LL RESIDENTIAL SPRINKLERS</b>			
12 Capacity	6803200000	A312CAB	\$ 481.16

### ESCUTCHEONS

Part Number	Short Code	Temperature	Finish	List Price
<b>ONE PIECE TYPE - MODEL B 1/2"</b>				
6800110000	BB	165°F	Bright Brass	\$ 4.26
6800150000	BC	165°F	Chrome	\$ 2.92
6800120000	BW	165°F	White	\$ 3.28
<b>ONE PIECE TYPE - MODEL B 3/4"</b>				
6800080000	BLB	165°F	Bright Brass	\$ 4.49
6800070000	BLC	165°F	Chrome	\$ 3.15
6800090000	BLW	165°F	White	\$ 3.15
<b>ONE PIECE TYPE - MODEL C 1/2"</b>				
6800340000	CBB	165°F	Bright Brass	\$ 32.40
6800350000	CC	165°F	Chrome	\$ 3.12
6800380000	CW	165°F	White	\$ 3.12
<b>TWO PIECE TYPE - MODEL HB 1/2"</b>				
6800210000	HBB	165°F	Bronze	\$ 7.41
6800270000	HBC	165°F	Chrome	\$ 6.67
6800200000	HBW	165°F	White	\$ 6.92
<b>TWO PIECE TYPE - MODEL HB 3/4"</b>				
6800220000	HBLB	165°F	Bronze	\$ 7.65
6800240000	HBLC	165°F	Chrome	\$ 6.92
6800250000	HBLW	165°F	White	\$ 7.41
<b>FLUSH ESCUTCHEONS - MODEL B</b>				
86791100	BFB	165°F	Bronze	\$ 51.69
86792100	BFC	165°F	Chrome	\$ 80.28
86797200	BFW	165°F	White	\$ 80.28



**ESCUTCHEONS**

Description	Part Number	Short Code	List Price
<b>MODEL FP PUSH-ON/THREAD-OFF ESCUTCHEONS</b>			
1/2" Chrome	6801412100	FPC	\$ 19.86
1/2" White	6801417200	FPW	\$ 19.86
3/4" Chrome	6801402100	FPLC	\$ 19.86
3/4" White	6801407200	FPLW	\$ 19.86
<b>MODEL F1 RECESSED ESCUTCHEONS &amp; COLLAR ASSEMBLY</b>			
1/2" Brass	6800630001	GF1B	\$ 19.09
1/2" Chrome	6800600001	GF1C	\$ 10.30
1/2" White	6800640001	GF1W	\$ 10.30
3/4" Brass	6801030000	GF1LB	\$ 19.09
3/4" Chrome	6801000000	GF1LC	\$ 10.30
3/4" White	6801040000	GF1LW	\$ 10.30
<b>ESCUTCHEON ONLY</b>			
Brass	6800430000	BZESCF1	\$ 14.56
Chrome Bright	6800400000	CBESCF1	\$ 6.19
White	6800440000	WHESCF1	\$ 6.19
<b>COLLAR ONLY</b>			
1/2" Brass	6800530000	B2COLLAR12	\$ 11.40
1/2" Chrome Bright	6800500000	CBCOLLAR12	\$ 9.35
1/2" White	6800540000	WHCOLLAR12	\$ 9.35
3/4" Brass	6800560004	B2COLLAR34	\$ Call
3/4" Chrome Bright	6800560001	CBCOLLAR34	\$ 9.35
3/4" White	6800551003	WHCOLLAR34	\$ 9.35
<b>ESCUTCHEON EXTENDER RING</b>			
Chrome	6814002100	EERC	\$ 13.23
White	6814001500	EERW	\$ 14.10
<b>F1 OR F2</b>			
4-1/2" Chrome	6814002100	EERC	\$ 13.23
4-1/2" White	6814001500	EERW	\$ 14.10
5-1/2" Chrome	6814042100	EERC5	\$ 13.23
5-1/2" White	6814041500		\$ 14.10
<b>FP / G4 / RFC43 / F4FR / CCP / SWC / DH80 / DH56</b>			
4-1/2" Chrome	6814022100	G4ERC	\$ 13.23
4-1/2" White	6814021800		\$ 14.10
5-1/2" Chrome	6814032100	G4ERC5	\$ 13.23
5-1/2" White	6814031800	G4ERW5	\$ 14.10

<b>MODEL F2 RECESSED ESCUTCHEONS &amp; COLLAR ASSEMBLY</b>			
1/2" Brass	6800830000	GF2B	\$ 19.09
1/2" Chrome	6800800000	GF2C	\$ 10.30
1/2" White	6800840000	GF2W	\$ 10.30
3/4" Brass	6800880004	GF2LB	\$ 19.09
3/4" Chrome	6800880001	GF2LC	\$ 10.30
3/4" White	6800880005	GF2LW	\$ 10.30
<b>ESCUTCHEON ONLY</b>			
Brass	6800730000	BZESCF2	\$ 14.46
Chrome	6800100000		\$ 9.32
White	6800740000	WHESCF2	\$ 9.32
<b>COLLAR ONLY</b>			
1/2" Brass	6800530000	B2COLLAR12	\$ 11.40
1/2" Chrome	6800500000	CBCOLLAR12	\$ 9.35
1/2" White	6800540000	WHCOLLAR12	\$ 9.35
3/4" Brass	6800560004	B2COLLAR34	\$ Call
3/4" Chrome	6800560001	CBCOLLAR34	\$ 9.35
3/4" White	6800551003	WHCOLLAR34	\$ 9.35

**G/F1 for use with SP & HSW Sprinklers**  
**G/F2 for use with SP & HSW Sprinklers**  
**G/F2 for use with SP & HSW Sprinklers**



**MP LL  
 Multipurpose  
 Residential Riser**

• See Bulletin 426

**Accessories**

Description	Part Number	Short Code	List Price
<b>MODEL MPLL MULTIPURPOSE RESIDENTIAL RISER</b>			
Model MP LL 1" (30mm)	6501200125	1MPLL	\$ 1,042.18
<b>RISER ACCESSORIES</b>			
Optional Support Bracket Kit	6899190001	RRB	\$ 101.63

Description	Part Number	Short Code	List Price
<b>PRESSURE GAUGES</b>			
WATER	98248001	WATER	\$ 104.00
AIR	98248000	AIR	\$ 111.20
Air (0-60 oz/in <sup>2</sup> )	98248002	AIRO	\$ 393.88
<b>INSPECTORS TEST CONNECTIONS</b>			
Sight Test Type (Model B)	6851010000	ISC	\$ 429.54
Blind Test Type (Model A)	6851020000	IBC	\$ 143.18
<b>AUTOMATIC BALL DRIPS</b>			
1/2" NPT (Female)	78653500	5ABD	\$ 249.12
3/4" NPT (Female)	78653700	75ABD	\$ 284.66
<b>MECHANICAL BALL DRIPS</b>			
1/2" NPT (Female)	78653100	5MBD	\$ 444.71
<b>STRAINER</b>			
3/4" NPT (Female)	78650200	34ST	\$ 261.36
<b>MISCELLANEOUS</b>			
Model C Sight Drain 2" NPT (Female)	6863000000	2ISC	\$ 465.93
Model B Drum Drip Only 3/4" NPT (Female)	71010448		\$ 285.63
Model A Fill Cup 1/2" NPT (Female)	75000050	5FC	\$ 134.81
Model A Fill Cup 3/4" NPT (Female)	75000075	75FC	\$ 152.53
Model A Control Valve Seal Only	6869800000		\$ 37.26
<b>SIGNS—MODEL A</b>			
Valve Control Sign	6892011000	VCS	\$ 17.19
<b>SIGNS—MODEL B</b>			
Inspector Test Sign	6892110000	ITS	\$ 3.34
Open Sprinkler Control Sign	6892030000	OSCS	\$ 3.58
Open Sprinkler Drain Sign	6892040000	OSDS	\$ 3.58
Test Valve Sign	6892050000	TVS	\$ 3.58
Water Motor Line Sign	6892060000	WMLS	\$ 3.58
Auxiliary Drain Sign	6892070000	ADS	\$ 3.34
Main Drain Sign	6892080000	MDS	\$ 3.34
Drain Sign	6892090000	DS	\$ 3.22
Alarm Test Sign	6892100000	ATS	\$ 3.58
<b>SIGNS—MODEL C</b>			
Cold Weather Sign	6892010000	CWS	\$ 12.00
<b>SIGNS—MODEL D</b>			
Fire Alarm Sign	6892020000	FAS	\$ 17.19
<b>SIGNS—MODEL E</b>			
Hydraulically Calculated System	6892120000	HCS	\$ 9.43

## ELECTRICAL COMPONENTS



Description	Part Number	Short Code	List Price
<b>MODEL WFDT - WATERFLOW DETECTOR</b>			
1" - 2", w/1" NPT T-Tap Waterflow	7M99003216	TTAPN	\$ 302.54
<b>ACCESSORIES</b>			
1 & 1-1/2" Waterflow Detector Gasket	6999990717		\$ 16.68
2 & 3-1/2" Waterflow Detector Gasket	6999990357		\$ 16.68
4 - 8" Waterflow Detector Gasket	6999990356		\$ 16.68
Repl. Terminal block			\$ Call
Repl. Timer	6999992444	TIMER	\$ 111.00
Waterflow Detector Tamper Switch Kit	6923000000	5467000	\$ 60.00
Wrench Cover (Key)	6999990769	WFDW	\$ 19.50
Cover	6999991174		\$ 29.00
<b>ELECTRIC ALARM BELLS &amp; HORN/STROBE</b>			
6" -- 24 VDC	6611220400	6KMS	\$ 91.25
8" -- 24 VDC	6611220500	8KMS	\$ 116.26
10" -- 24VDC	6611220600	10KMS	\$ 132.32
BRK MA Polarized Sounder -- 24 VDC	6999993325	HORNWBB24	\$ 170.97
BRK MASS Polarized Sounder Strobe (#P2R)	6990006617	P2RL	\$ 131.00
P2RHK-120	6990001425	HORNWBB	\$ 194.65
6" -- 120 VAC	6611221100	6KBS	\$ 91.25
8" -- 120 VAC	6611221200	8KBS	\$ 116.26
10" -- 120 VAC	6611221300	10KBS	\$ 132.32
WBB Weatherproof Back Box	6611660200	WBB	\$ 49.97